

Rittal – The System.

Faster – better – everywhere.

LED system light – SZ 2500.213

Date : Sep 22, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



LED system light – SZ 2500.213

created: 22.09.2020 build on www.rittal.com/in-en



Product description

Design:	with socket
Benefits:	Optimum illumination of the entire enclosure Optionally with clip, screw and magnetic attachment A configuration to suit every application
Equipment:	Socket 90° rotating connector Adjustable light distribution
Material:	Light body: Extruded aluminium Light cover: Polycarbonate (halogen-free) Light ends: PC-ABS (halogen-free)
Colour:	Enclosure: RAL 7016
Protection category IP to IEC 60 529:	IP 20
Supply includes:	Assembly screws

Product features

Dimensions:	Width: 437 mm Height: 80 mm Depth: 44 mm
Rated operating voltage:	100 V - 240 V, 1~, 50 Hz/60 Hz
Installation options:	Directly onto the enclosure section with 25 mm pitch pattern

Operating temperature:	Operation (environment): -20 °C...+55 °C
Power consumption:	11 W
Equipment (electrical):	Jack/socket (type): CH (type J, SEV 1011)
Rated insulation voltage:	300 V AC
Rated impulse withstand voltage, phase to earth:	2500 V AC
Luminous flux:	900 lm
Light colour:	4000 K (neutral white)
Protection class:	II (all-insulated)
Overvoltage category:	II
Connection options:	Infeed, 3-pole Through-wiring, 3-pole Door-operated switch
Light – installation type:	Screw-fastening Clip attachment
Packs of:	1 pc(s).
Weight/pack:	0.61 kg
Copper weight (kg per piece):	0
EAN:	4028177811331
Customs tariff number:	94054099
ETIM 7.0:	EC000321
ETIM 6.0:	EC000321
eCl@ss 8.0/8.1:	27189241
eCl@ss 6.0/6.1:	27189241
Product description:	SZ System Light LED, 900 Lumen, L: 437 mm, 100-240 V, with earthing-pin socket for Switzerland

Approvals

Approvals:	CCC ENEC
-------------------	-------------

Certificates:	EAC
----------------------	-----

Declarations:	Declaration of conformity
----------------------	---------------------------