

Rittal – The System.

Faster – better – everywhere.

EMC cable glands – SZ 2843.500

Date : Sep 29, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EMC cable glands – SZ 2843.500

created: 29.09.2020 build on www.rittal.com/lt-en



Product description

Design: Cable glands, metric

Description: The cable sheathing may optionally be interrupted at the contact point or removed completely inside the enclosure. The cable shielding in the enclosure is retained. The supplied lock nut cuts automatically into the paint when screwed onto spray-finished enclosure surfaces, thus creating a conductive connection.

**Protection category
IP to IEC 60 529:** IP 68

**Protection category
IP to DIN 40 050-9:** IP 69K

Note: Minimum shield diameter = cable diameter less cable sheathing

Product features

**Shield diameter
(min.):** 19 mm

Min. cable diameter: 27 mm

Max. cable diameter: 38 mm

Cable entry: Metric diameter: M50

Packs of: 1 pc(s).

Weight/pack: 0.34 kg

Copper weight (kg) 0

per piece):

EAN: 4028177247062

Customs tariff number: 74199990

ETIM 7.0: EC000441

ETIM 6.0: EC000441

eCl@ss 8.0/8.1: 27149109

eCl@ss 6.0/6.1: 27189214

Product description: SZ EMC cable glands, metric, size: M50

Approvals

Approvals: UL + C-UL
VDE

Certificates: EAC

Declarations: Declaration of conformity