

Rittal – The System.

Faster – better – everywhere.

Thermostat Enclosure internal thermostat – SK 3110.000

Date : Sep 27, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Thermostat Enclosure internal thermostat – SK 3110.000

created: 27.09.2020 build on www.rittal.com/nz-en



Product description

Description:	Particularly suitable for controlling fans, heaters and heat exchangers, this thermostat can also be used as a signal generator for monitoring the enclosure internal temperature.
Benefits:	Time-saving connection technique using a terminal strip with a screw connection from the outside. Flexible mounting on a vertical or horizontal 35 mm support rail to EN 50 022, and snap fastening in the enclosure section or on the mounting plate using the supplied adaptor
Technical specifications:	Bi-metal controller as a temperature-sensitive element with thermal feedback Contact population: Single-pole change-over contact as a quick-break contact Permissible contact load: Category 5 – 3 (heating) AC 10 (4) A (inductive load at $\cos \varphi = 0.6$)/category 5- 4 (cooling): AC 5 (4) A (inductive load at $\cos \varphi = 0.6$)/DC = max. 30 W Switching difference: approx. 1 K \pm 0.8 K
Colour:	RAL 7035
Product features	
Rated operating voltage:	24 V - 230 V, 1~ 24 V - 60 V (DC)
Dimensions:	Width: 71 mm Height: 71 mm Depth: 33.5 mm
Temperature range:	Setting range: +5 °C...+60 °C
eCI@ss 8.0/8.1:	27210707

Packs of:	1 pc(s).
Weight/pack:	0.1 kg
EAN:	4028177036598
Customs tariff number:	90321020
ETIM 7.0:	EC002014
ETIM 6.0:	EC002014
eCl@ss 8.0/8.1:	27210707
eCl@ss 6.0/6.1:	27210707
Product description:	SK Thermostat, enclosure internal thermostat, 24-230 V, 1~, 24-60 V (DC), Colour RAL 7035, WHD: 71 x 71 x 33.5 mm
Approvals	
Approvals:	CCC exception letter UL + C-UL VDE
Certificates:	EAC
Declarations:	Declaration of conformity