

Rittal – The System.

Faster – better – everywhere.

Assembly frame – AS 4050.150

Date : Aug 5, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Assembly frame – AS 4050.150

created: 05.08.2020 build on www.rittal.com/nz-en



Product description

Design:	150 MN (manually tilt-adjustable)
Description:	The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures.
Benefits:	For ergonomic, back-friendly working Individually positionable in the workshop, as it is independent from the power network Minimum space requirements during non-use Simple handling due to four castors including total lock function Variable fixing of mounting plates with a quick-release fastener
Note:	With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved.
Technical specifications:	Tilt adjustment approx. 0 – 80°
Supply includes:	Assembly frame 1 clamping unit pack, bottom 1 clamping unit pack, top
Note:	With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved.

Product features

Load capacity:	150 kg
Working height (min./max.):	100 cm / 100 cm
Dimensions:	Width: 1400 mm

Depth: 1250 mm

Dimensions of support surface (W x H) min.:	1110 mm x 1230 mm
Dimensions of support surface (W x H) max.:	1110 mm x 1900 mm
Packs of:	1 pc(s).
Weight/pack:	138 kg
Copper weight (kg per piece):	0
EAN:	4028177804609
Customs tariff number:	84279000
ETIM 7.0:	EC002224
ETIM 6.0:	EC002224
eCl@ss 8.0/8.1:	36659090
eCl@ss 6.0/6.1:	36659090
Product description:	Assembly frame 150 MN
Approvals	
Declarations:	Declaration of conformity