

Rittal – The System.

Faster – better – everywhere.

Polycarbonate enclosures PK with knockouts – PK 9508.050

Date : Oct 1, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Polycarbonate enclosures PK with knockouts – PK 9508.050

created: 01.10.2020 build on www.rittal.com/nz-en



Product description

Applications:	Ambient temperature range: -35 °C...+80 °C The specified temperatures may be limited by the installed equipment
Material:	Enclosure: Fibreglass-reinforced polycarbonate Cover: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 66
Protection category NEMA:	NEMA 4X
IK Code:	IK08
Supply includes:	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Basic material:	Polycarbonate

Product features

Dimensions:	Width: 130 mm Height: 94 mm Depth: 57 mm
--------------------	--

Cover:	grey
Ambient temperature range:	-35 °C...+80 °C
Cable entry:	Number x metric diameter: 10 x M16/M20
Packs of:	4 pc(s).
Weight/pack:	0.88 kg
EAN:	4028177490192
Customs tariff number:	94037000
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	PK Polycarbonate enclosure, WHD: 130x94x57 mm, fibreglass-reinforced polycarbonate, with knockouts, with grey cover
Approvals	
Approvals:	C-UL DNV-GL UL
Declarations:	Declaration of conformity