# Rittal – The System.

Faster – better – everywhere.





# KL 1522.010 Terminal boxes KL

State: 10/11/2025 (Source: rittal.com/au-en)



## KL 1522.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

## **Features**

Model No.	KL 1522.010	
Material Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foal		
Surface finish	Enclosure and cover: Brushed, grain 180	
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes	
Protection category NEMA	NEMA 4X	
Protection category to IEC 60 529	IP 66	
IK Code	IK08	
Dimensions	Width: 300 mm Height: 150 mm Depth: 80 mm	
Material thickness - cover	1.25 mm	
Material thickness - enclosure	1.25 mm	
Lock	Number of locks: 4	
Basic material	Stainless steel 1.4301 (AISI 304)	
Packs of	1 pc(s).	
Net weight	1.673	
Gross weight	1.94	
Customs tariff number	84879090	
EAN	4028177008465	
E-Number Sweden	E3404364	
ETIM 9	EC000261	
ETIM 8	EC000261	

© Rittal 2025

#### **Features**

SS 8.0 27180101
-----------------

## **Approvals**

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

#### Tender text

Stainless steel terminal box without gland plate, protection cat. IP 66

**Enclosure:** 

of 1.25 mm stainless steel 1.4301 (AISI 304), folded and welded from a single piece, with all-round protection channel on the cover aperture. Cover of 1.25 mm stainless steel, sealed, with foamed-in special cover seal, facilities for connecting PE conductors in the cover and box, profile strips on both internal sides with mounting holes. Special plastic bush guards against accidental loss of the cover screws and provides screwdriver guidance.

Accessories:

quick-release fastener, cover retainer, plastic cable gland plate, cover hinges, mounting plate Surface finish:

brushed

Dimensions (W x H x D): 300 x 150 x 80 mm

© Rittal 2025 3