


Rittal – The System.

Faster – better – everywhere.



SG 2369.000

Steady light component

State: 21/05/2024 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2369.000 - Steady light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system, number of potential stages = 5 components, with identical voltage.

Features

Model No.	SG 2369.000
Design	Steady light component
Product description	With 360° signal transmission thanks to optimised prism system. No. of potential stages = 5 components, with identical voltage.
Benefits	Simple assembly and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colours and voltages.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Material	Enclosure of polyamide Cap: Transparent polycarbonate
Colour	Red
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Note on Model No.	Incandescent lamps not included with the supply.
Dimensions	Height: 56 mm
Protection category to IEC 60 529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	12 V - 240 V (AC/DC)
Packs of	1 pc(s).
Weight/pack	0.086 kg
Customs tariff number	85311095

Features

EAN	4028177219922
ETIM 7.0	EC000232
ECLASS 8.0	27371220

Approvals

Approvals	C-UL UL + C-UL (listed) UR
-----------	----------------------------------