Rittal – The System.

Faster - better - everywhere.







SG 2372.102 - Signal pillar 3-way LED

Identify malfunctions and operating statuses in machines and automated processes immediately with Rittal's flexible range of signal pillars to suit all applications. If you only need three standard signal colours, the plug-and-play 3-way LED signal system is the ideal choice.

Features

| Model No. | SG 2372.102 |
|-----------------------------------|--|
| Design | for wall/base mounting |
| Benefits | Complete, ready-to-connect solution Extremely long service life of the LEDs (max. 100,000 hours, therefore maintenance-free) Minimal assembly work and warehousing costs |
| Technical specifications | 3-stage, red, yellow, green Transmission angle: 3 x 120° |
| Cable entry | Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm |
| Type of electrical connection | Screwless spring terminals |
| Light | LEDs |
| Dimensions | Height: 211.5 mm |
| Operating temperature range | -20 °C50 °C |
| Protection category to IEC 60 529 | IP 65 |
| Rated operating voltage | 24 V |
| Thread | M12 x 1.5 |
| Packs of | 1 pc(s). |
| Net weight | 0.25 |
| Gross weight | 0.309 |
| Customs tariff number | 85318070 |
| EAN | 4028177953765 |
| ETIM 9 | EC001042 |

© Rittal 2025 2

Features

| ETIM 8 | EC001042 | |
|------------|----------|--|
| ECLASS 8.0 | 27371230 | |

© Rittal 2025 3