


# Rittal – The System.

Faster – better – everywhere.



## SM 2376.100 AS interface element

State: 25/07/2025 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SM 2376.100 - AS interface element for signal pillar, modular

For user-friendly activation of the signal pillar levels via AS interface.



## Features

Model No.	SM 2376.100
Technical specifications	Standard slave Max. 31 addresses Up to 4 signal levels may be activated. Power supply may be switched from internal bus supply to external auxiliary voltage With programming interface
Material	Polycarbonate
Colour	Black, transparent
Diameter	70 mm
External auxiliary voltage	External auxiliary voltage 24 V DC $\pm$ 10% Current carrying capacity max. 200 mA per rack Current rating max. 75 mA Voltage on signal element 24 V DC $\pm$ 10% Short-circuit/overload protection: Pre-fuse M 1.6 A

# Features

Internal auxiliary voltage	Voltage supply via bus cable Current carrying capacity max. 200 mA Current rating max. 250 mA Voltage on signal element 18 – 31 V DC Short-circuit/overload protection: Built-in
Dimensions	Height: 56 mm
Operating temperature range	-20 °C...50 °C
Protection category to IEC 60 529	IP 54
Packs of	1 pc(s).
Net weight	0.119
Gross weight	0.12
Customs tariff number	39269097
EAN	4028177580350
ECLASS 8.0	27371220

# Approvals

Approvals	UR
-----------	----