

# Rittal – The System.

Faster – better – everywhere.



## HD 2410.111 Cable gland HD

State: 25/01/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# HD 2410.111 - Cable gland HD

More compact design and the lock nut is included with the supply.



## Features

Model No.	HD 2410.111
Design	EMC
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Lock nut
Dimensions	Thread: M16 x 1.5
For cable diameters	5 - 10 mm
Operating temperature range	-20 °C...100 °C

## Features

---

IP protection category to IEC 60  
529 IP69 / IPX8 (5 bar, 30 min)

---

Packs of 5 pc(s).

---

Net weight 0.2

---

Gross weight 0.206

---

Customs tariff number 73072980

---

EAN 4028177928671

---

ETIM 9 EC000441

---

ETIM 8 EC000441

---

ECLASS 8.0 27149109

---

## Approvals

---

Approvals UR + C-UR (recognized)  
VDE