

Rittal – The System.

Faster – better – everywhere.



SZ 2843.160

EMC cable glands

State: 2/07/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2843.160 - EMC cable glands

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

| | |
|-------------------------------------|--|
| Model No. | SZ 2843.160 |
| Design | Cable glands, metric |
| Product description | The cable sheathing may optionally be interrupted at the contact point or removed completely inside the enclosure. The cable shielding in the enclosure is retained. The supplied lock nut cuts automatically into the paint when screwed onto spray-finished enclosure surfaces, thus creating a conductive connection. |
| Material | Brass Seal: CR/NBR |
| Surface finish | Nickel-plated |
| Note | Minimum shield diameter = cable diameter less cable sheathing |
| Min. cable diameter | 4.5 mm |
| Max. cable diameter | 10 mm |
| Protection category IP 69K | IP 69K |
| IP protection category to IEC 60529 | IP 68 |
| Shield diameter (min.) | 3 mm |
| Type rating to UL 50E | Type 4X |
| Packs of | 5 pc(s). |
| Net weight | 0.15 kg |
| Gross weight | 0.157 kg |
| Customs tariff number | 74198090 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |

Features

ECLASS 8.0

27149109

Product description

SZ EMC cable glands, metric, size: M16

Approvals

Approvals

UR + C-UR (recognized)
VDE

Explanations

Declaration of conformity
Declaration of conformity UK