

**Rittal – The System.**

Faster – better – everywhere.



**SK 3108.100**

**Enclosure internal fan**

State: 8/02/2026 (Source: [ittal.com/au-en](http://ittal.com/au-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SK 3108.100 - Enclosure internal fan

To prevent hot-spots inside the enclosure and support the air routing of active enclosure climate control components.



## Features

Model No.	SK 3108.100
Product description	To prevent hot-spots and support the air routing of active enclosure climate control components. Adjustable in two axes. Attached to the frame section. Several fans may be cascaded using the quick-release clamping strip.
Supply includes	Complete unit with axial fan ready for connection Snap-on pivot device Assembly parts
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 19 W At 60 Hz: 18 W
Rated current max.	At 50 Hz: 0.12 A At 60 Hz: 0.11 A
Packs of	1 pc(s).
Net weight	0.94
Gross weight	1.126
Customs tariff number	84145915
EAN	4028177220485

## Features

---

ETIM 9 EC000320

---

ETIM 8 EC000320

---

ECLASS 8.0 27180716

## Approvals

---

Explanations Declaration of conformity