

Rittal – The System.

Faster – better – everywhere.



SK 3130.100

TopTherm air-air heat exchanger

State: 7/08/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3130.100 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

Features

Model No.	SK 3130.100
Design	wall-mounted
Product description	Air/air heat exchangers are particularly well-suited to aggressive ambient conditions, because the internal and external air circuits are completely separate from one another.
Colour	RAL 7035
Supply includes	Complete unit ready for connection Plug-in terminal strip Floating fault signal contact in case of overtemperature Drilling template Assembly parts
Specific thermal output	90 W/K
Air throughput (unimpeded air flow)	External circuit with 50 Hz: 850 m³/h External circuit with 60 Hz: 945 m³/h Internal circuit at 50 Hz: 850 m³/h Internal circuit at 60 Hz: 945 m³/h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 1.35 A At 60 Hz: 1.8 A
Dimensions	Width: 400 mm Height: 1,580 mm Depth: 215 mm
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Temperature control	Electronic control with digital display (factory setting +35 °C)
Operating temperature range	-5 °C...55 °C

Features

IP protection category to IEC 60529	Internal circuit IP 54 External circuit IP 34
Packs of	1 pc(s).
Net weight	37.05
Gross weight	39
Customs tariff number	84158300
EAN	4028177388994
ETIM 9	EC002514
ETIM 8	EC002514
ECLASS 8.0	27180711

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK