

Rittal – The System.

Faster – better – everywhere.



SK 3201.960

Toroidal transformer

State: 14/02/2026 (Source: rittal.com/au-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3201.960 - Toroidal transformer Primary connection 115 V/400 V

For power supply to wall-mounted 230 V air/water heat exchangers. Available with 115 V or 400 V primary connection.

Features

Model No.	SK 3201.960
Product description	For the power supply of wall-mounted 230 V air/water heat exchangers. Available with 115 V or 400 V primary connection.
Technical specifications	<p>Output 110 VA</p> <p>Voltage tolerance $\pm 10\%$</p> <p>Primary connection 3500 mm long</p> <p>Secondary connection 1500 mm long</p> <p>For mounting on a 35 mm support rail EN 50 022</p>
Supply includes	Toroidal transformer Assembly parts
Packs of	1 pc(s).
Snap-mounting to support rails TS 35	Yes
To fit Model No.	3363.X0X 3364.X0X 3212.230 3214.100 3214.700 3215.100 3215.700
Dimensions	Width: 105 mm Height: 123 mm Depth: 55 mm
Rated operating voltage	230 V (secondary), 1~, 50 Hz/60 Hz 400 V (primary), 2~, 50 Hz/60 Hz
Net weight	2.2

Features

Gross weight 3.214

Customs tariff number 85043121

EAN 4028177690226

ETIM 9 EC000855

ETIM 8 EC000855

ECLASS 8.0 27180704

Approvals

Certificates EAC

Explanations Declaration of conformity