

Rittal – The System.

Faster – better – everywhere.



SK 3216.480

Air-water heat exchangers

State: 15/05/2025 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3216.480 - Air-water heat exchangers wall-mounted

Output category 7000 W. For use in harsh environments. With thermostat-controlled magnetic valve.



Features

Model No.	SK 3216.480
Design	Water-carrying parts, copper/brass (Cu/CuZn)
Product description	For use in harsh environments and temperature ranges up to +70 °C. With thermostatically controlled magnetic valve.
Material	Copper/brass (Cu/CuZn)
Colour	RAL 7035
Supply includes	Fully wired ready for connection (plug-in terminal strip) Sealing and assembly parts
Total cooling output	L 35 W 10 at 500 l/h: 7 kW
Rated operating voltage	400 V, 3~, 50 Hz 480 V, 3~, 60 Hz
Rated current max.	At 50 Hz: 1.4 A At 60 Hz: 1.6 A 1.2 A
Permissible operating pressure (p. max.)	1 - 10 bar
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)

Features

Water inlet temperature	1 °C...30 °C
Water connections	½" connector sleeve G ¾" external thread
Temperature control	Thermostat-controlled magnetic valve
Temperature monitoring	Internal thermostat, with change-over contact, switching load 16 A, setting range +20 °C ... +60 °C (factory setting +35 °C)
Operating temperature range	1 °C...70 °C
Note	Use 3-pole miniature circuit-breaker
Dimensions	Width: 450 mm Height: 1,800 mm Depth: 300 mm
Note on Model No.	Extended delivery times.
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Pre-fuse	Motor circuit-breaker: 1.4...2 A
Setting range	20 °C...55 °C
Protection category to IEC 60 529	IP 55
Packs of	1 pc(s).
Net weight	80
Gross weight	90
Customs tariff number	84158300
EAN	4028177458642
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

Approvals

Approvals	CSA
-----------	-----

Tender text

Wall-mounted air/Water heat exchanger

For use in tough environments.

With thermostat-controlled magnetic valve.

Total cooling output:

L 35 W 10, 500l/h: 7 kW

L 35 W 20, 500l/h: 4.5 kW

Rated operating voltage: 400/460 V, 50/60 Hz

Refrigerant: Water (see specifications)

Water-carrying parts: Cu/CuZn

Dimensions [W x H x D]: 450 x 1800 x 300 mm

Ambient temperature range: 1°C to 70°C

Setting range: 20°C to 55°C

Water inlet temperature range: 1°C to 30°C

Temperature control and monitoring:

Thermostat-controlled magnetic valve

Type of connection: Plug-in terminal strip

Protection category to IEC 60 529: IP 55

Weight: 79 kg

Colour: RAL 7035