

Rittal – The System.

Faster – better – everywhere.



SK 3238.025 Pleated filter

State: 10/07/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3238.025 - Pleated filter for fan-and-filter units, roof-mounted fans, cooling units and chillers

The high-quality pleated filter technology permits a significant increase in the volumetric air flow compared to conventional chopped-fibre filter mats. Cooling unit performance is improved and energy consumption is lower. The enhanced filtration properties also mean less dust in the enclosure or unit, and the resulting longer maintenance intervals reduce service costs significantly.

Features

Model No.	SK 3238.025
Design	for filter fans / outlet filters
Material	Pleated filter: Based on polyester, meltblown polycarbonate Absorber mat: 100% polyester
Colour	White
Note	No suitable for use in EMC filter fans.
To fit Model No.	3238.3xx 3238.7xx
Dimensions	Width: 114 mm Height: 114 mm Depth: 14 mm
Dimensions of absorber mat	Width: 120 mm Height: 120 mm
IP protection category to IEC 60529	IP 55 in fan-and-filter units/outlet filters
Packs of	5 pc(s).
Net weight	0.1 kg
Gross weight	0.113 kg
Customs tariff number	56039390
ETIM 9	EC002513

Features

ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK Pleated filter IP 55, for fan-and-filter units/outlet filters 3238.7xx/3238.3xx, WxHxD: 114x114x14 mm

Approvals

Approvals	CSA UR + C-UR (recognized)
-----------	-------------------------------