

# Rittal – The System.

Faster – better – everywhere.



## SK 3305.140

## Wall-mounted cooling units

State: 16/12/2025 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3305.140 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.

## Features

Model No.	SK 3305.140
Material	Sheet steel
Supply includes	Fully wired ready for connection Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 1,500 W Cooling output L35 L35/60 Hz: 1,510 W Cooling output L35 L50/50 Hz: 1,230 W Cooling output L35 L50/60 Hz: 1,250 W
Rated operating voltage	400 V, 3~, 50 Hz 460 V, 3~, 60 Hz
Rated current max.	At 50 Hz: 2.6 A At 60 Hz: 2.9 A
Start-up current max.	At 50 Hz: 12.2 A At 60 Hz: 11.3 A
Air throughput (unimpeded air flow)	External circuit: 900 m³/h Internal circuit: 800 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.6
Design	wall-mounted
Dimensions	Width: 400 mm Height: 950 mm Depth: 260 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54

# Features

Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.6 kg Global Warming Potential (GWP): 1,430 CO2 equivalent (CO2e): 0.86 t
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	20 °C...55 °C
Setting range	30 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 925 W Power consumption L35 L35/60 Hz: 1,100 W Power consumption L35 L50/50 Hz: 1,085 W Power consumption L35 L50/60 Hz: 1,275 W
Pre-fuse	Motor circuit-breaker: 6.3...10 A
Packs of	1 pc(s).
Net weight	46.551
Gross weight	49.001
Customs tariff number	84158200
EAN	4028177322974
ECLASS 8.0	27180704

# Approvals

Approvals	UL + C-UL (listed)
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK

# Tender text

Wall-mounted cooling unit Rittal TopTherm PLUS  
with RiNano coating and integral condensate evaporation  
Useful cooling output to DIN 3168 L35 L35 1500/1510 W  
Rated operating voltage 400 V, 3~, 50 Hz -  
460 V, 3~, 60 Hz  
Power consumption Pel to DIN 3168 L35 L35 925/1100 W  
Dimensions W x H x D [mm] 400 x 950 x 260  
Refrigerant R 134 a  
Temperature range 20°C to 55°C (Setting range +30°C to +55°C)  
Temperature control and monitoring via basic  
controller with floating fault signal contact  
and connection for door operated switch  
Factory setting 35°C  
Connection by pluggable terminal strip  
Protection category to EN 60 529/10.91  
External circuit IP 34/Internal circuit IP 54  
Weight 42 kg  
Colour RAL 7035