

Rittal – The System.

Faster – better – everywhere.



SK 3361.610

TopTherm wall-mounted cooling unit Blue e

State: 28/06/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3361.610 - TopTherm wall-mounted cooling unit Blue e 0.3 - 4 kW

Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W). Available in the special formats "horizontal" and "flat".



Features

Model No.	SK 3361.610
Design	wall-mounted
Benefits	May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Stainless steel 1.4301 (AISI 304)
Colour	RAL 9007
Supply includes	Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/60 Hz: 0.87 kW Cooling output L35 L50/60 Hz: 0.51 kW
Rated operating voltage	115 V, 1~, 60 Hz
Rated current max.	At 60 Hz: 6.63 A
Start-up current max.	At 60 Hz: 11.5 A
Air throughput (unimpeded air flow)	External circuit: 480 m ³ /h Internal circuit: 600 m ³ /h

Features

Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 60 Hz: 1.58
Design	wall-mounted
Dimensions	Width: 280 mm Height: 550 mm Depth: 280 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.26 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.16 t
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Operating temperature max @60 Hz	52 °C
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...52 °C
Power consumption Pel	Power consumption L35 L35/60 Hz: 0.55 kW Power consumption L35 L50/60 Hz: 0.6 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Packs of	1 pc(s).
Net weight	21.546 kg
Gross weight	22.68 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855

Features

ECLASS 8.0	27180704
------------	----------

Product description	SK Cooling unit Blue e, wall-mounted, 0.75 kW, 115 V, 1~, 60 Hz, stainless steel, WxHxD: 280 x 550 x 280 mm
---------------------	-------------------------------------------------------------------------------------------------------------

Approvals

Approvals	UL + C-UL (listed) UL + C-UL - FTTA UR + C-UR (recognized)
-----------	------------------------------------------------------------------

Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK
--------------	-----------------------------------------------------------------------------------------------------------