

Rittal – The System.

Faster – better – everywhere.



SK 3375.510

Air/water heat exchangers

State: 4/06/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3375.510 - Air/water heat exchangers wall-mounted

Output classes 375 – 5,000 W. For use in tough environments. Convenient mounting options and flexible water connection options. External mounting or full internal mounting possible.

Features

| | |
|--|--|
| Model No. | SK 3375.510 |
| Design | wall-mounted Water-carrying parts, copper/brass (Cu/CuZn) |
| Product description | For use in harsh environments and temperature ranges up to +70 °C. User-friendly assembly plus flexible water connection options. External mounting or full internal mounting are supported. |
| Colour | RAL 7035 |
| Supply includes | Fully wired ready for connection Drilling template Sealing and assembly parts |
| Total cooling output | L 35 W 10 at 400 l/h: 5 kW |
| Rated operating voltage | 115 V, 1~, 50 Hz/60 Hz 110 V (DC) |
| Power consumption Pel | At 50 Hz: 178 W At 60 Hz: 232 W |
| Rated current max. | At 50 Hz: 2.25 A At 60 Hz: 2.25 A |
| Permissible operating pressure (p. max.) | 1: 10 bar |
| Duty cycle | 100 % |
| Cooling medium | Water (see Internet for specifications) |
| Water inlet temperature | 1 °C...30 °C |
| Water connections | ½" connector sleeve G ¾" external thread |
| Temperature control | e-Comfort controller (factory setting +35 °C) |

Features

| | |
|-----------------------------------|--|
| Operating temperature range | 1 °C...70 °C |
| Note | Integral non-return valve for version with e-Comfort controller |
| Dimensions | Width: 450 mm Height: 1,400 mm Depth: 220 mm |
| Note on Model No. | Extended delivery times. |
| Setting range | 20 °C...55 °C |
| Pre-fuse | Transformer circuit-breaker: 3.5...5 A |
| Protection category to IEC 60 529 | IP 55 |
| Protection category NEMA | UL Type 1 UL Type 3R UL Type 12 |
| Packs of | 1 pc(s). |
| Net weight | 96.561 lb |
| Gross weight | 101.411 lb |
| Customs tariff number | 8415830070 |
| ETIM 9 | EC002515 |
| ETIM 8 | EC002515 |
| ECLASS 8.0 | 27180712 |
| Product description | SK Air/water heat exchanger, wall-mounted, 5 kW, 115 V, 1~, 50/60 Hz, comfort controller, water-carrying parts: copper/brass, WHD: 450 x 1400 x 220 mm |

Approvals

| | |
|--------------|---|
| Approvals | CSA UL + C-UL - FTTA UR + C-UR (recognized) |
| Explanations | Declaration of conformity |