
### Rittal – The System.

Faster – better – everywhere.





# SV 3439.010 Connection adaptor

State: 17/11/2025 (Source: rittal.com/au-en)



## SV 3439.010 - Connection adaptor

For bar systems with 60 mm centre-to-centre spacing.

#### **Features**

Model No.	SV 3439.010
Material	Cover: ABS Chassis: Fibreglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated current max.	600 A
Rated operating voltage	690 V, 3~
Cable outlet	Top/bottom
For bar systems with centre-to- centre spacing	60 mm
Note	The technical data may vary for UL applications UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar supports 9340.050/9341.050/9342.050.
Number of poles	3-pole
Dimensions	Width: 180 mm Height: 247 mm
Connection of round conductors, multi-wire	35 - 240 mm²
To fit busbars	Height: 5, 10 mm
Clamping area for laminated copper bars (W x H)	24 x 21 mm
Packs of	1 pc(s).
Net weight	4.36
Gross weight	4.635

© Rittal 2025

#### **Features**

Copper weight (kg per piece)	0.732
Customs tariff number	85369010
EAN	4028177236295
ETIM 9	EC001531
ETIM 8	EC001531
ECLASS 8.0	27370304

## **Approvals**

Approvals	ABS
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3