

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.454

## Crimping machine R8 E

State: 5/02/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AS 4050.454 - Crimping machine R8 E

Electrically driven wire stripping and crimping machine for taped wire end ferrules on a reel.



## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4050.454   |
| Design                   | Touchscreen display   |
| Product description      | Electrically powered wire stripping and crimping machine for taped wire end ferrules on a reel.   |
| Benefits                 | <ul style="list-style-type: none"><li>Easy to operate</li><li>Fast adjustment</li><li>Flexible use in the workshop</li><li>Rapid replacement of consumables</li></ul>                   |
| Technical specifications | <ul style="list-style-type: none"><li>Crimping range 0.5 - 2.5 mm<sup>2</sup> (AWG 20 - 14)</li><li>Crimping length 8 mm (0.31 in.)</li><li>Insertion length 40 mm (1.57 in.)</li></ul> |
| Note                     | The standard crimping form is trapezoid – others available on request   |
| Dimensions               | <ul style="list-style-type: none"><li>Width: 288 mm</li><li>Height: 230 mm</li><li>Depth: 345 mm</li></ul>  |
| Rated operating voltage  | 100 V - 240 V, 1~, 50 Hz/60 Hz  |
| Apparent power           | 100 VA  |
| Compression              | Trapezoid crimp   |
| Cycle time               | 1.8 s   |
| Packs of                 | 1 pc(s).  |

# Features

---

|                       |               |
|-----------------------|---------------|
| Net weight            | 16            |
| Gross weight          | 16            |
| Customs tariff number | 84798997      |
| EAN                   | 4028177813465 |
| ETIM 9                | EC002778      |
| ETIM 8                | EC002778      |
| ECLASS 8.0            | 36600890      |

---