

Rittal – The System.

Faster – better – everywhere.



AS 4054.023 Crimping pliers

State: 14/05/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.023 - Crimping pliers for ring terminals

For use with non-insulated ring terminals



Features

Model No.	AS 4054.023
Design	Straight
Product description	For use with non-insulated ring terminals.
Benefits	Releasable ratchet Optimised lever transmission means that only minimal actuator forces are required, even with large cross-sections
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Double-indent crimp
Dimensions	Height: 68 mm Length: 256 mm
AWG	12 - 8
For cross-section	4 - 10 mm ²
Packs of	1 pc(s).
Net weight	0.63 kg
Gross weight	0.668 kg
Customs tariff number	82032000

Features

ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	Crimping plier 4 - 10 mm ² , d-indent
