

Rittal – The System.

Faster – better – everywhere.



SV 3563.000 Plate clamp

State: 14/08/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3563.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

Features

| | |
|---|--|
| Model No. | SV 3563.000 |
| Product description | For connecting laminated copper bars, no drilling required. |
| Material | Sheet steel |
| Surface finish | Zinc-plated, passivated |
| Clamping area for laminated copper bars (W x H) | 54 x 10 mm |
| To fit busbars | 60 x 10 |
| To fit busbars | Busbar E-Cu |
| Packs of | 3 pc(s). |
| Net weight | 1.35 |
| Gross weight | 1.569 |
| PCF per pack (cradle-to-gate) | 6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 85369010 |
| EAN | 4028177044418 |
| ETIM 9 | EC000001 |
| ETIM 8 | EC000001 |
| ECLASS 8.0 | 27141146 |

Approvals

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

Plate clamps

for E-Cu busbars with 3 - 10 mm thickness.

For bar width: up to 60 mm

Clamping area for laminated copper bars:

54 x 10 mm

Tightening torque: 6 - 8 Nm

Material: Sheet steel, zinc-plated, passivated