

Rittal – The System.

Faster – better – everywhere.



SV 3586.020 CUPONAL busbars

State: 6/04/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3586.020 - CUPONAL busbars

Copper-coated aluminium busbar



Features

Model No.	SV 3586.020
Product description	Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050.
Material	Aluminium Copper
Rated current max.	493 A
Note	The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature Correction factor diagram to DIN EN 43 671 May be cut individually to required length
Standards	DIN EN 13 601
Cross-section	30 mm x 10 mm
Dimensions	Length: 2,400 mm
Packs of	3 pc(s).
Net weight	7.5 kg
Gross weight	9.2 kg
Copper weight (kg per piece)	1.05
Customs tariff number	74071000

Features

ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303
Product description	SV Busbar CUPONAL, WH: 30x10 mm, L: 2400 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---