

Rittal – The System.

Faster – better – everywhere.



AS 4050.452

Crimping machine L8

State: 10/02/2026 (Source: rittal.com/au-en)



AS 4050.452 - Crimping machine L8

Electro-pneumatically powered wire stripping and crimping machine for loose, insulated wire end ferrules.

Features

Model No.	AS 4050.452
Design	Touchscreen display
Product description	Electro-pneumatically driven wire stripping and crimping centre for loose, insulated wire end ferrules.
Benefits	<p>Easy to operate</p> <p>Secure, fast processing of insulated wire end ferrules</p> <p>No set-up time, thanks to automatic tool change</p> <p>Handling of special wires supported</p> <p>Simple, quick component mounting</p> <p>Automatic detection of cross-sections</p>
Technical specifications	<p>Crimping range 0.5 - 2.5 mm² (AWG 20 - 14)</p> <p>Crimping length 8 mm (0.31 in.)</p> <p>Insertion length 35 mm (1.38 in.)</p> <p>Processing of wire end ferrules with plastic collars in special sizes supported</p>
Supply includes	<p>Crimping machine L8</p> <p>1 vibratory bowl feeder 0.5 - 1.5 mm²</p> <p>1 vibratory bowl feeder 1.5 - 2.5 mm²</p>
Note	The standard crimping form is trapezoid – others available on request
Dimensions	<p>Width: 390 mm</p> <p>Height: 460 mm</p> <p>Depth: 330 mm</p>
Compressed air connection	5.5 bar
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	110 VA
Compression	Trapezoid crimp

Features

Cycle time	1.5 s
Packs of	1 pc(s).
Net weight	34.6
Gross weight	34.67
Customs tariff number	84798997
EAN	4028177804869
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890