


# Rittal – The System.

Faster – better – everywhere.



## AS 4050.737 Wire end ferrules

State: 13/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.737 - Wire end ferrules loose

With plastic collar.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4050.737   |
| Design                   | for manual wire processing<br>for Wire Terminal WT C fully automated wire processing machine  |
| Product description      | With plastic collar.  |
| Technical specifications | Heat-resistant to 105 °C  |
| Material                 | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene  |
| Colour                   | White   |
| Length                   | 12 mm   |
| AWG                      | 20  |
| Internal diameter        | 2.6 mm  |
| For cross-section        | 0.5 mm <sup>2</sup>   |
| DIN colour code          | Yes   |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines.<br>For bespoke advice, please contact your Rittal sales consultant. |
| Standards                | AEH DIN 46228   |
| To fit Model No.         | 4051.205<br>4051.210  |
| Delivery form            | Loose (10 packs of 100)   |
| Packs of                 | 1,000 pc(s).  |
| Net weight               | 1 kg  |
| Gross weight             | 0.105 kg  |
| Customs tariff number    | 85369010  |

# Features

---

|                     |  |
|---------------------|--|
| ETIM 9              | EC000005   |
| ETIM 8              | EC000005   |
| ECLASS 8.0          | 36659290   |
| Product description | Wire end ferrules for wire processing, 0.5 mm <sup>2</sup> , white, loose, 12 mm, 10x100 |

# Approvals

---

|           |                          |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed)<br>UR |
|-----------|--------------------------|