

Rittal – The System.

Faster – better – everywhere.



AS 4055.581

Splitter hole punch set, M12 to M40

State: 8/02/2026 (Source: rittal.com/au-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4055.581 - Splitter hole punch set, M12 to M40 for sheet steel, with triple splitting

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.581 |
| Design | With triple splitting |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | 6 female dies 6 male dies Tension screw with ball bearing Ø 6 x 40 mm Tension screw with ball bearing Ø 9.5 x 50 mm Tension screw with ball bearing Ø 19 x 55 mm HSS pilot drill Ø 10 mm 1 can of lubricant paste Plastic case |
| Machinable material | Sheet steel |
| Maximum machinable material thickness, sheet steel | 1.5 mm 2 mm 2 mm 2 mm 3 mm 3 mm |
| Ø punch | 12.5 mm 16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm |

Features

| | |
|--|---|
| For threads | M12 M16 M20 M25 M32 M40 |
| Note | When operating with wrenches, tension screws with ball bearings should be used. |
| Suitable for hydraulic bolt order number | 4055.660 4055.661 4055.661 4055.661 4055.663 4055.663 |
| Packs of | 1 pc(s). |
| Net weight | 2.2 |
| Gross weight | 2.256 |
| Customs tariff number | 82073010 |
| EAN | 4028177808843 |
| ETIM 9 | EC002121 |
| ETIM 8 | EC002121 |
| ECLASS 8.0 | 21044719 |