

Rittal – The System.

Faster – better – everywhere.



SZ 4140.220 Compact light

State: 22/06/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4140.220 - Compact light

Compact light – slimline, space-saving light for use inside the enclosure



Features

| | |
|----------------------------|--|
| Model No. | SZ 4140.220 |
| Benefits | <p>Slimmer: Around 50% less height and depth and therefore around 75% less volume than conventional lights</p> <p>Faster: Universal fast attachment to the TS slots via clips, screws, or powerful magnets (optional). Simply slide in at the side or rear, fit the light, and it's done!</p> <p>Door-operated switch can also be connected via a 2-pole connector</p> <p>Transparent light cover, grooved on the inside</p> |
| Colour | Similar to RAL 7035 |
| Supply includes | <p>Compact light with clip and screw mounting kits</p> <p>Light</p> <p>Light cover</p> <p>Connection cable</p> <p>Assembly parts</p> |
| Power consumption | 14 W |
| Length of connection cable | 3 m |
| Mounting distance screws | 725 mm |

Features

| | |
|---|---|
| Ballast | Wide-range electronic ballast |
| Connection options | Integral connection cable with open end Door-operated switch |
| Light | Fluorescent lamp T5 |
| Protection class | II (all-insulated) |
| Switch (type) | Integral on/off/door-operated switch |
| Light cover | Yes |
| Light – installation type | Screw-fastening Clip attachment Magnetic attachment (accessory) |
| Rated impulse withstand voltage, phase to earth | 1000 V AC |
| Rated impulse withstand voltage, phase to phase | 500 V AC |
| Rated insulation voltage | 500 V DC/1s |
| Mounting distance clip/magnet | 650 mm |
| Installation options | TS horizontal section of the roof frame: direct TS, SE vertical section: direct SE extrusions at the front and rear of the roof frame: direct SE extrusions at the side of the roof frame: direct AE, CM, TP: with magnet mounting kit AE: with rail for interior installation |
| Note | Door-operated switch can also be connected via a 2-pole connector |
| Dimensions | Width: 705 mm Height: 59 mm Depth: 24 mm |
| Operating temperature range | -15 °C...45 °C |
| OUT_RATED_CURRENT_110_60 | 0.149 - 0.216 A |
| Rated current | 0.073 - 0.127 A |
| Storage temperature range | -20 °C...70 °C |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |

Features

| | |
|-------------------------------------|--|
| IP protection category to IEC 60529 | IP 20 |
| Packs of | 1 pc(s). |
| Net weight | 0.759 kg |
| Gross weight | 0.76 kg |
| Customs tariff number | 94054990 |
| ECLASS 8.0 | 27189241 |
| Product description | SZ Compact light, WHD: 705x59x24 mm, 14 W, 100-240 V, 50/60 Hz, Integral on/off/door-operated switch mode, cURus |

Approvals

| | |
|-----------|--|
| Approvals | UL + C-UL (listed) UR + C-UR (recognized) |
|-----------|--|