


# Rittal – The System.

Faster – better – everywhere.



## VX 5302.022 Combination rails

State: 8/07/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5302.022 - Combination rails for VX, VX IT, TX CableNet

Combination of a C rail for cable clamping with cable clamps and a cable guide rail with T-heads for cable routing. The cables can optionally be secured to the combination rail with cable clamps, cable ties or velcro fasteners to be relieved of strain.

## Features

Model No.	VX 5302.022
Product description	Combination of a C rail for cable clamping with cable clamps and a cable guide rail with T-heads for cable routing. The cables can optionally be secured to the combination rail with cable clamps, cable ties or velcro fasteners to be relieved of strain.
Benefits	May be installed on either the outside or inside of the enclosure frame
Applications	For cable routing and strain relief of routed cables on the VX frame structure
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Installation options	Direct screw-fastening between the vertical uprights of the enclosure frame
To fit	Enclosure type: VX VX IT TX CableNet Width: = 1,000 mm Depth: = 1,000 mm
Suitable for width	1,000 mm
Packs of	4 pc(s).
Net weight	1.72 kg
Gross weight	2.62 kg

# Features

PCF per pack (cradle-to-gate)	9.9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC000322
ECLASS 8.0	27400604
Product description	Combination rail for VX IT, for cable routing and strain relief of routed cables on the VX frame structure, for enclosure width 1,000 mm, for enclosure depth 1,000 mm