

Rittal – The System.

Faster – better – everywhere.



DK 5501.480

Slide rail, 1 U, depth-variable

State: 3/04/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.480 - Slide rail, 1 U, depth-variable for VX IT, TE, TX CableNet

For mounting between a front and a rear pair of mounting angles.



Features

Model No.	DK 5501.480
Benefits	Tool-free, time-saving one-man assembly from the enclosure front All three mounting holes in the EIA system punchings are available for screw-fastening the equipment. Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm (19") system punchings is also possible
Applications	For mounting on the front mounting level To support heavy installed equipment To adapt to individual distances between 482.6 mm (19") levels
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Installation options	482.6 mm (19") L mounting angles, front and rear 482.6 mm (19") mounting frames front and rear 482.6 mm (19") mounting angles, standard in the VX IT
Load capacity	1500 N
Note	Effective contact surface 25 mm per side

Features

To fit	Enclosure type: TS IT VX IT TE TX CableNet
Distance between levels	600 - 900 mm
Packs of	2 pc(s).
Net weight	3.2 kg
Gross weight	3.74 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Slide rail, support surface Width: 25 mm, depth-variable, 150 kg, For two 482.6 mm (19") attachment level (front+rear), distance between levels:: 600-900 mm

Tender text

482.6 mm (19") - slide rails, depth-variable

Depth-variable slide rails for L-shaped mounting angles and similar shapes of mounting angles.

For mounting between a pair of mounting angles and to support heavy installed equipment.

Distance between 482.6 mm (19") levels from 600-900 mm, load capacity 150 kg.

The slide rails have vent holes across the entire depth to support the climate control of integral components.

Tool-free, time saving one-man assembly from the enclosure front.

Locate, pull-out, snap into position.

All three mounting holes in the 482.6 mm (19") system punchings are available for screw-fastening the equipment.

Material: Sheet steel

Surface finish: Zinc-plated

Model No DK: 5501.480

Manufacturer: Rittal