

Rittal – The System.

Faster – better – everywhere.



CX 6723.000

CX console

State: 11/07/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6723.000 - CX console

Four widths create the ideal conditions for individual monitoring and three-piece assembly of the CX console system.



Features

| | |
|---------------------|--|
| Model No. | CX 6723.000 |
| Design | Console |
| Product description | Four widths create the ideal conditions for individual monitoring and three-piece assembly of the CX console system. |
| Material | Enclosure: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm, all-round foamed-in PU seal |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure Cover hinged at bottom, including cover retainer Open base for individual cable entry Lock: 3 mm double-bit |
| Dimensions | Width: 1,600 mm Height: 515 mm |
| Depth (top) | 125 mm |
| Depth (bottom) | 245 mm |
| IK Code | IK10 |
| Note | A desk unit and pedestal are required for a 3-part console assembly. |

Features

| | |
|-------------------------------------|--|
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 1 NEMA 12 |
| Basic material | Sheet steel |
| Dimensions | Width: 1,600 mm Height: 515 mm Depth (top): 125 mm Depth (bottom): 245 mm |
| Number of locks | 3 |
| Lock version | Cam |
| Lock insert | 3 mm double-bit |
| Lock | Lock version: Cam Number of locks: 3 Lock insert: 3 mm double-bit |
| Packs of | 1 pc(s). |
| Net weight | 39 kg |
| Gross weight | 40 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |
| Product description | CX console system, console for 3-part assembly, W: 1600 mm, sheet steel |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |