

# Rittal – The System.

Faster – better – everywhere.



DK 7338.221

Early fire detection system

State: 31/01/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 7338.221 - Early fire detection system EFD III

The EFD system is a compact 482.6 mm (19"), 1 U early fire detection system with active smoke extraction system.

## Features

Model No.	DK 7338.221
Product description	The EFD III early fire detection system includes the smoke extraction system in a 482.6 mm (19") subrack with just 1 U. An integral fan continuously extracts air from the area being protected via a system of pipes. The air drawn in passes two fire detectors. If smoke is detected, the highly sensitive detector will emit a pre-alarm, while the second detector will activate the main alarm. The fire detectors are permanently monitored for correct functioning by the evaluation and control electronics on the control card.
Benefits	Early fire detection 482.6 mm (19") rack mount with just 1 U Tested by VdS Schadenverhütung GmbH CAN bus interface to the CMC III monitoring system Floating relay outputs (pre-alarm/main alarm/collective fault)
Material	Sheet steel
Colour	Enclosure: RAL 7035 Front: RAL 9005
Interfaces	4 x/3 x relay outputs for alarms and faults (terminals/RJ12 jacks) 1 x/1 x input for door contact switch (terminal/RJ12 jack) 2 x CAN connections for master-slave networking 3 x connection (external alarm/manual call point/tank and fill level) 1 x voltage output for DET-AC slave III (24 V DC max. 500 mA) 1 x USB 2 x CAN bus interfaces to CMC III (max. 16 on PU/4 on PU Compact)
Uninterruptible mains electricity operation	approx. 4 h
Note	This system is designed solely for use in closed, non-accessible enclosure systems.

# Features

Display	Plain-language display with 6 LEDs
Sensors	Optical smoke detector (sensitivity: approx. 3.5%/m light obscuration) Optical smoke detector HS (sensitivity: approx. 0.25%/m light obscuration)
Dimensions	Width: 482.6 mm Height: 44 mm Depth: 490 mm
Operating temperature range	10 °C...40 °C
Storage temperature range	-20 °C...65 °C
Storage temperature range of batteries	-15 °C...40 °C
Relative humidity (non-condensing)	96 %
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Air flow monitoring	approx. ±10% of total airflow
Packs of	1 pc(s).
Net weight	14
Gross weight	15
PCF per pack (cradle-to-gate)	57.2 kg CO <sub>2</sub> eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85311095
EAN	4028177699328
ETIM 9	EC002685
ECLASS 8.0	40040104

# Approvals

# Approvals

---

Certificates	VDS
Explanations	Declaration of conformity

---

# Tender text

## EFD III early fire detection system

The early fire detection system is able to detect fires at an early stage. The compact system occupies 1 U of rack space and is designed for installation in the 19" level of closed server enclosure systems.

An integrated fan continuously draws in air from the protected space via a pipe system. This air passes two smoke detectors. If smoke aerosols are detected, the high-sensitivity smoke detector triggers a pre-alarm state. The second smoke detector triggers the main alarm. The proper functioning of the smoke detectors is monitored continuously by the evaluation and control electronics on the control board.

Alarms and fault messages can be output and forwarded to a higher-level system (monitoring or control system) via floating contacts.

An integrated CAN bus interface enables direct connection to the CMC III system.

As an option, the early fire detection system offers a possibility to control an external extinguishing agent tank. When the second fire alarm threshold is reached, the relay output "Main alarm" and the output for the external extinguishing agent tank are triggered.

The commissioning must be carried out by Rittal.

Technical data:

Width: 482.6 mm (19")

Height: 44 mm (1 U)

Depth: 490 mm

Housing material: Sheet steel

Weight: approx. 9.6 kg

Rated voltage: 100-240 V AC, 50/60 Hz

Emergency power supply: approx. 4 h

Max. permissible active current: 1.0 A at 24 V (the sum of all connected devices must not exceed the permissible active current of 1.0 A)

Max. permissible charging current: 350 mA at 24 V

Ambient temperature:

+10 °C to +40 °C (operation),

-20 °C to +65 °C (storage without batteries),

-15 °C to +40 °C (battery storage)

Humidity: up to 96% (relative), non-condensing

Protection category: IP 30

Connections:

Terminal for relay output "Pre-alarm", "Fire alarm", "Extinguishing"

Terminal for relay output "Collective fault"  
Terminal for door contact switch  
Socket (RJ 12) for connection of door contact switch  
3x sockets (RJ 12) for signal outputs "Fault", "Pre-alarm", "Main alarm"  
2x CAN connection for system networking  
Connection for external alarm device  
Connection for external filling level monitoring and control of an external tank, max. 500 mA  
Connector for manual alarm  
Voltage supply (UB), max. 500 mA  
USB port  
CAN bus interface to CMC III  
Displays:  
1 plain-language display for status messages  
1 LED green, "Operation"  
1 LED yellow, "Shutdown"  
1 LED red, "Extinguishing system primed"  
1 LED red, "Extinguishing system activated"  
1 LED yellow, "Blocked"  
1 LED yellow, "Fault"  
Sensors (2 different scattered-light sensors for 2 alarm thresholds):  
Optical smoke detector  
(sensitivity: approx. 3.5%/m obscuration)  
Optical smoke detector HS  
(sensitivity: approx. 0.25%/m obscuration)  
Air flow monitoring: approx. +/-10% of overall air flow  
External devices:  
Connection for manual alarm  
Connection for door contact  
Connection for external alarm device  
CAN bus interface to Rittal CMC III  
Model No.: 7338.221  
Manufacturer: Rittal GmbH & Co. KG