

Rittal – The System.

Faster – better – everywhere.



DK 7827.140

Mounting angles, 482.6 mm (19")

State: 22/05/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.140 - Mounting angles, 482.6 mm (19") for TS, CS Toptec

Mounting angles in cranked design Mounting angles are available in an L-shape as an alternative.

Features

| | |
|--------------------------|---|
| Model No. | DK 7827.140 |
| Design | Cranked |
| Benefits | Integral U markings in the front facilitate systematic assembly within the 482.6 mm (19") attachment level. |
| Technical specifications | Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of the 482.6 mm (19") installed equipment. |
| Material | Sheet steel, 2 mm |
| Supply includes | Assembly parts |
| Dimensions | Width: 482.6 mm |
| Units | 29 U |
| Note | The mounting angles can also be used to accommodate 21", 23" and 24" attachment dimensions. Please select slide rails according to the relevant 482.6 mm (19") distance between levels. If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used. |
| To fit | Enclosure type: TS 8 CS Toptec Height: 1,400 mm |
| Packs of | 2 pc(s). |
| Net weight | 4.17 kg |
| Gross weight | 4.34 kg |
| Customs tariff number | 73269098 |

Features

| | |
|------------|----------|
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Tender text

DK-TS mounting angle, 29 U

Technical specifications: 2 mm steel sheet, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and square holes. Zinc-plated, passivated for conductive connection to the installed 482.6 mm (19") equipment.

Material: Sheet steel, zinc-plated, passivated