

# Rittal – The System.

Faster – better – everywhere.



## SR 7858.100 Swing frame, large, with trim panel

State: 7/12/2025 (Source: [rittal.com/en/usa](https://rittal.com/en/usa))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SR 7858.100 - Swing frame, large, with trim panel for TS, VX SE 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel, for mounting 482.6 mm (19") equipment.

## Features

Model No.	SR 7858.100
Design	Heavy-duty version, 482.6 mm (19") level at the side
Product description	For mounting 482.6 mm (19") equipment.
Material	Sheet steel
Surface finish	Frame: Zinc-plated Trim panel: Spray-finished
Colour	RAL 7035
Supply includes	Locking rod system with double-bit lock insert Material for attaching Installation kit for enclosure height 2000 mm
Opening angle	130°
Assembly instruction	Depending on the mounting situation, TS punched sections with mounting flanges 23 x 73 mm or 17 x 73 mm are required
Note	For further installation options, see "Technical details" For two-door enclosures TS, SE with a height of 1800 or 2200 mm the next-smallest swing frame must be installed, due to collision with the lock
Load capacity (static)	350 kg
To fit	Enclosure type: TS VX SE Width: = 800 mm Height: = 2,000 mm
Units	40 U
To fit enclosure type	TS VX SE

# Features

Packs of	1 pc(s).
Net weight	24.757
Gross weight	26.06
Customs tariff number	94039910
EAN	4028177438880
ETIM 9	EC002620
ECLASS 8.0	27189261

## Tender text

482.6 mm (19 inch) heavy-duty swing frame, 40 U

1 swing frame with trim panel, including locking rod with double-bit lock insert, heavy-duty installation kit and assembly parts.

Material: Swing frame: Sheet steel, zinc-plated, passivated

Trim and installation kit: Sheet steel, spray finished in RAL 7035

Load capacity: 350 kg