

# Rittal – The System.

Faster – better – everywhere.



## DK 7827.221

## Mounting angles, 482.6 mm (19")

State: 18/04/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7827.221 - Mounting angles, 482.6 mm (19") for TS

L-shaped mounting angles, also for accommodating server system installation kits.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | DK 7827.221   |
| Design                   | L-shaped mounting angle   |
| Benefits                 | Integral U markings in the front facilitate systematic assembly within the 482.6 mm (19") attachment level.<br>L-shaped mounting angles accommodate the installation kits of server systems<br>Suitable for 482.6 mm (19") partial installation |
| Technical specifications | Integral 482.6 mm (19") punchings (EIA standard)<br>Side round and square punchings<br>Clear chromated for conductive connection of the 482.6 mm (19") installed equipment.   |
| Material                 | Sheet steel, 2 mm   |
| Supply includes          | Assembly parts  |
| Units                    | 47 U  |
| Note                     | Please select slide rails according to the relevant 482.6 mm (19") distance between levels.<br>If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used.  |
| To fit                   | Enclosure type: TS<br>Height: 2,200 mm  |
| Packs of                 | 2 pc(s).  |
| Net weight               | 4.958 kg  |
| Gross weight             | 5.218 kg  |
| Customs tariff number    | 73269098  |
| ETIM 9                   | EC002620  |
| ECLASS 8.0               | 27189261  |

# Features

---

Product description

DK-TS Mounting angles, 482.6 mm (19"), L-shaped mounting angle,  
For H: 2200 mm, 47 U

## Tender text

DK-TS mounting angles, L-shaped, 47 U

Technical specifications: 2 mm sheet steel, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and square holes. Zinc-plated, passivated for conductive connection to the installed 482.6 mm (19") equipment.

Material: Sheet steel, zinc-plated, passivated