


Rittal – The System.

Faster – better – everywhere.



SR 7858.100 Swing frame, large, with trim panel

State: 10/08/2025 (Source: [rittal.com/usa/en](https://www.rittal.com/))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SR 7858.100 - Swing frame, large, with trim panel for TS, VX SE 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel, for mounting 482.6 mm (19") equipment.

Features

| | |
|------------------------|--|
| Model No. | SR 7858.100 |
| Design | Heavy-duty version, 482.6 mm (19") level at the side |
| Product description | For mounting 482.6 mm (19") equipment. |
| Material | Sheet steel |
| Surface finish | Frame: Zinc-plated Trim panel: Spray-finished |
| Colour | RAL 7035 |
| Supply includes | Locking rod system with double-bit lock insert Material for attaching Installation kit for enclosure height 2000 mm |
| Opening angle | 130° |
| Assembly instruction | Depending on the mounting situation, TS punched sections with mounting flanges 23 x 73 mm or 17 x 73 mm are required |
| Note | For further installation options, see "Technical details" For two-door enclosures TS, SE with a height of 1800 or 2200 mm the next-smallest swing frame must be installed, due to collision with the lock |
| Load capacity (static) | 350 kg |
| To fit | Enclosure type: TS VX SE Width: = 800 mm Height: = 2,000 mm |
| Units | 40 U |
| To fit enclosure type | TS VX SE |

Features

| | |
|-----------------------|---------------|
| Packs of | 1 pc(s). |
| Net weight | 24.757 |
| Gross weight | 26.06 |
| Customs tariff number | 94039910 |
| EAN | 4028177438880 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Tender text

482.6 mm (19 inch) heavy-duty swing frame, 40 U

1 swing frame with trim panel, including locking rod with double-bit lock insert, heavy-duty installation kit and assembly parts.

Material: Swing frame: Sheet steel, zinc-plated, passivated

Trim and installation kit: Sheet steel, spray finished in RAL 7035

Load capacity: 350 kg