Rittal – The System.

Faster – better – everywhere.





VX 8660.042 Base/plinth trim panels, side

State: 6/11/2025 (Source: rittal.com/au-en)



VX 8660.042 - Base/plinth trim panels, side for base/plinth system VX, sheet steel

To finish off a base/plinth unit at the sides and for additional stability or interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.







Features

Model No.	VX 8660.042
Design	Solid
Material	Sheet steel
Colour	RAL 9005
Supply includes	Assembly parts
Dimensions	Height: 200 mm
To fit	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
TP PC IW	TP
	PC
	CX
	Depth: = 500 mm

© Rittal 2025 2

Features

Type rating to UL 50E	Type 1 Type 12	
Weight/pack	2.52 kg	
Packs of	2 pc(s).	
To fit	for base/plinth system VX, sheet steel	
Net weight	2.38	
Gross weight	2.524	
PCF per pack (cradle-to-gate)	9.6 kg CO2 eq (Cat B)	
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared	
Customs tariff number	94039910	
EAN	4028177978300	
ETIM 9	EC000721	
ETIM 8	EC000721	
ECLASS 8.0	27182003	

Approvals

planations PCF-declaration	Explanations

© Rittal 2025 3