

Rittal – The System.

Faster – better – everywhere.



KEL 9306.000

Ex enclosures

State: 7/02/2026 (Source: rittal.com/au-en)



FRIEDHELM LOH GROUP

KEL 9306.000 - Ex enclosures stainless steel, empty enclosure with screw-fastened cover

Ex enclosure with screw-fastened cover, stainless steel



Features

Model No.	KEL 9306.000
Design	Ex enclosures
Applications	<p>Zone 1 and 2 or 21 and 22 to 2014/34/EC</p> <p>Ambient temperature range: -30 °C...+80 °C</p> <p>The specified temperatures may be limited by the installed equipment</p> <p>Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)</p>
Material	<p>Enclosure: Stainless steel 1.4301 (AISI 304)</p> <p>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal</p>
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Enclosure Cover
Dimensions	<p>Width: 300 mm</p> <p>Height: 300 mm</p> <p>Depth: 120 mm</p>

Features

Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
IP protection category to IEC 60 529	IP 66
Packs of	1 pc(s).
Net weight	3.7
Gross weight	3.9
Customs tariff number	94032080
EAN	4028177138643
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals	ATEX
	ATEX QA
	CQC-CCC
	IECEx
	IECEx QAR
