

Rittal – The System.

Faster – better – everywhere.



SV 9340.950

Bus-mounting fuse base D-Switch

State: 11/08/2025 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.950 - Bus-mounting fuse base D-Switch

With integral visual fuse monitoring via flashing indicator and operating status display.

Features

Model No.	SV 9340.950
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035 Fuse holder: RAL 7001
Supply includes	Retaining springs for D 01 and 10 x 38 mm fuses
Note	Wire end ferrules should be used with fine wire conductors
For bar systems with centre-to-centre spacing	60 mm
Type of electrical connection	Box terminal
Fuse inserts	D 01 (with retaining spring) D 02 (with Neozed adaptor sleeve) 10 x 38 (with retaining spring)
Fuse inserts footnote	When using D01 and 10 x 38 mm fuses, reducing retaining springs must be used. Use of D 01 fuses optionally possible with adaptor sleeve for D 02 base/plinths.
Rated operating current max.	63 A
Rated operating voltage	400 V, 3~
Note	For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3) With integral visual fuse monitoring via flashing indicator and operating status display as well as cable routing for conductors up to 6 mm ²
Test specification	IEC/DIN EN 60 947-3
Dimensions	Width: 27 mm Height: 226 mm
Connection of round conductors	1.5 - 25 mm ²

Features

To fit busbars	Height: 5, 10 mm
Voltage range for indicator lights	100 - 400 V
Number of poles	3-pole
Packs of	3 pc(s).
Net weight	0.975
Gross weight	1.04
Copper weight (kg per piece)	0.066
Customs tariff number	85369095
EAN	4028177603400
ETIM 9	EC001046
ECLASS 8.0	27371402

Approvals

Explanations	Declaration of conformity
--------------	---------------------------