

Rittal – The System.

Faster – better – everywhere.



SV 9340.050 Busbar support

State: 24/08/2025 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.050 - Busbar support for flat copper busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.050
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated operating voltage	1000 V, 3~ 1500 V (DC)
Electrical ratings UL (SCCR)	14 kA - 600 V, support spacing 500 mm, 12 x 5/10 mm busbars 22 kA - 600 V, support spacing 500 mm, 15 x 5 - 25 x 10 mm busbars 25 kA - 600 V, support spacing 250 mm, 12 x 5/10 mm busbars 25 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars 30 kA - 600 V, support spacing 250 mm, 15 x 5 - 25 x 10 mm busbars 50 kA - 600 V, support spacing 350 mm, 30 x 5/10 mm busbars, Fuse Class L max. 800 A, JDDZ/7 54 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars, circuit breaker max. 600 A, DIVQ/7 65 kA - 480 V, support spacing 250 mm, 30 x 5/10 mm busbars, circuit breaker max. 600 A, DIVQ/7 73 kA - 600 V, support spacing 250 mm, 30 x 5/10 mm busbars, Fuse Class L max. 800 A, JDDZ/7
Note on Model No.	The use of a base tray is required for UL applications UL approval only applies in conjunction with AC application
Number of poles	3-pole
Internal attachment	Yes
Centre-to-centre spacing of busbars	60 mm
To fit busbars	12 x 5 - 30 x 10
Packs of	4 pc(s).

Features

Net weight	0.668
Gross weight	0.72
Customs tariff number	85369010
EAN	4028177525573
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

UL busbar support
UL busbar support with internal attachment, 3-pole
Technical specifications
Bar centre distance: 60 mm
Busbars E-Cu, 15 x 5 to 30 x 10 mm
Construction width: 20 mm
Length: 190 mm
Note
The use of a base tray is compulsory for
UL applications.
System:
Rittal RiLine60