

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.620 OM adaptors

State: 20/12/2025 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.620 - OM adaptors with spring terminals



## Features

Model No.	SV 9340.620
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Rated current max.	65 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to-centre spacing	60 mm
Support rail type	without support frame, 1 x TS 55E, 1 x TS 55D
Number of poles	3-pole
Note on Model No.	According to a heat dissipation test to IEC 61 439-1, a current carrying capacity of up to 80 A is supported
Dimensions	Width: 55 mm Height: 208 mm
Connection of round conductors	2.5 - 16 mm <sup>2</sup>
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Packs of	1 pc(s).
Net weight	0.299

# Features

---

Gross weight	0.348
--------------	-------

---

Copper weight (kg per piece)	0.059
------------------------------	-------

---

Customs tariff number	85369095
-----------------------	----------

---

EAN	4028177561786
-----	---------------

---

ETIM 9	EC001531
--------	----------

---

ECLASS 8.0	27370304
------------	----------

# Approvals

---

Approvals	ABS DNV-GL Lloyds Register of Shipping
-----------	--

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---

# Tender text

OM adaptor 65 A

OM adaptor 65 A with tension spring clamp, 3-pole,  
for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 55 mm

Length: 208 mm

Support frame: -

Support frame support: -

Support rail: 2

System:

Rittal RiLine60