

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.710 OM adaptors

State: 13/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.710 - OM adaptors with connection cables



## Features

Model No.	SV 9340.710
Design	With connection cable
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Connection cables (AWG)	AWG 8
Rated current max.	40 A
Rated operating voltage	690 V, 3~
Electrical ratings UL (SCCR)	30 kA - 600 V, Fuse Class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, Fuse Class J max. 60 A, JDDZ/7 65 kA - 480 V, Manual Motor Controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7
For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	130 mm
Support rail type	without support frame, 2 x 7.5 x 35 mm
Note	The technical data may vary for UL applications
Number of poles	3-pole
Dimensions	Width: 75 mm Height: 208 mm

# Features

---

Support rails Qty/height	2 / 7.5 mm
To fit busbars	Height: 5, 10 mm
Approvals	UL
Packs of	1 pc(s).
Net weight	0.379 kg
Gross weight	0.396 kg
Copper weight (kg per piece)	0.088
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 40 A, 690 V, 3-pole, connection cable AWG 8, WH: 75x208 mm, 2 insert strips, 2 metal support rails

# Approvals

---

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

# Tender text

OM adaptor 40 A

OM adaptor 40 A with connection cable, 3-pole,  
for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Connection cable: AWG 8 / approx. 10 qmm

Construction width: 75 mm

Length: 208 mm

Support frame: -mm

Support frame support: -

Insert strips: -

Support rail: 2

System:

Rittal RiLine60