


# Rittal – The System.

Faster – better – everywhere.



## SV 9345.005 Fuse holders

State: 13/06/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.005 - Fuse holders 31 A to 60 A

Fuse holders up to 60 A, 3-pole. Simple mounting on support rails or via OM component adaptors on busbars.

## Features

Model No.	SV 9345.005
Design	For category CC fuse type
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection for round conductor	AWG 8 - 18
Note	For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/supports)
Type of electrical connection	Box terminal
For fuse type (class)	CC
Rated operating current max.	30 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-4
Test specification	UL 4248-1 UL 4248-4 UL 4248-8
Note on Model No.	Not suitable for accommodating fuses 10 x 38 mm to IEC 60 269-2/-4/-6
Dimensions	Width: 54 mm Height: 81 mm
Connection of round conductors	0.75 - 25 mm <sup>2</sup>
To fit fuses	Diameter: 10 mm Length: 38 mm

# Features

---

Voltage range for indicator lights	110 - 600 V
Electrical ratings UL (SCCR)	200 kA - 600 V, Fuse Class CC max. 30 A, JDDZ/7
Number of poles	3-pole
Round conductor cross-section	0.75 - 25 mm <sup>2</sup>
Packs of	4 pc(s).
Net weight	0.4 kg
Gross weight	0.634 kg
Copper weight (kg per piece)	0.018
Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27400613
Product description	SV Fuseholder, Class CC, 30 A, 600 V, 3-pole, (60 mm)

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK