

Rittal – The System.

Faster – better – everywhere.



SV 9345.604

Circuit-breaker component adaptor

State: 15/05/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.604 - Circuit-breaker component adaptor 4-pole

Features

| | |
|---|--|
| Model No. | SV 9345.604 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Supply includes | Connection straps Sliding blocks |
| Rated current max. | 250 A |
| Rated operating voltage | 690 V, 4~ |
| Electrical ratings UL (SCCR) | 65 kA - 480 V, circuit breaker max. 250 A, DIVQ/7 |
| Cable outlet | Top |
| For bar systems with centre-to-centre spacing | 60 mm |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications |
| Number of poles | 4-pole |
| Dimensions | Width: 140 mm Height: 310 mm |
| To fit busbars | Height: 5, 10 mm |
| To fit manufacturer (model) | ABB (T3S, XT3) Eaton (NZM2-4/250 A) Schneider Electric (NS(X)100, NS(X)160, NS(X)250) Schrack (MC2) Siemens (VL160X, VL160, VL250, 3RV10 63, 3VA12/20/21/22, 3VA61/62) |
| Packs of | 1 pc(s). |
| Net weight | 2.405 kg |
| Gross weight | 2.516 kg |

Features

| | |
|------------------------------|--|
| Copper weight (kg per piece) | 1.134 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Circuit-breaker component adaptor, 250 A, 690 V, 4-pole, cable outlet top, with connection straps |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV Lloyds Register |
| Explanations | Declaration of conformity Declaration of conformity UK |