## Rittal – The System.

Faster – better – everywhere.





# RX 9360.780 RiLineX component adaptor

State: 28/11/2025 (Source: rittal.com/au-en)



## RX 9360.780 - RiLineX component adaptor

RiLineX component adaptor (80 A, 3-pole, including connection cables) in width 54 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.

#### **Features**

Model No.	RX 9360.780
Design	With connection cable
Benefits	For mounting equipment for top hat rail installation, e.g. motor starter
	Pre-assembled connection cable
	Simple clip locking for support rails
	Optional anti-slip guard
	Snap-on mounting and simple adjustment for busbar thickness
	(5/10 mm)
	Simple assembly
	Coordinated accessories reduce the number of different items required
Material	Polyamide (PA 6)
	Fire protection corresponding to UL 94
Colour	RAL 9005
	RAL 35745
Connection cables (AWG)	AWG 4
Rated current of round conductor	80 A
Rated current of round conductor (UL)	80 A
Cable outlet	Тор
For bar systems with centre-to- centre spacing	60 mm
Length of connection cable	130 mm
Number of poles	3-pole

© Rittal 2025 2

### Features

To fit busbar system	RiLineX RiLine60
Dimensions	Width: 54 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C55 °C
Storage temperature range	-25 °C75 °C
Ambient humidity (non-condensing)	1090 %
Packs of	4 pc(s).
Net weight	2.12
Gross weight	2.15
Copper weight (kg per piece)	0.209
Customs tariff number	85369095
EAN	4028177996984
ETIM 9	EC001531

© Rittal 2025 3

## Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025