

Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX connection adaptor

State: 14/02/2026 (Source: rittal.com/au-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

RX 9361.300 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. To fit double connection (bar). Freely selectable phase difference. Only suitable for 10 mm busbars.



Features

| | |
|---|---|
| Model No. | RX 9361.300 |
| Benefits | Mounting on the busbar system and cable connection with just one screw |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 9005 |
| Rated current of laminated copper bar | 1,500 A |
| Rated current of laminated copper bar (UL) | 1,380 A |
| Electrical ratings UL (SCCR) | 52.5 kA - 600 V, RMS, unprotected 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 100 kA - 600 V, Fuse Class L max. 2000 A, JDDZ/7 |
| Cable outlet | Top/bottom |
| For bar systems with centre-to-centre spacing | 60 mm |
| Number of poles | Single-pole |

Features

| | |
|---|--|
| To fit busbar system | RiLineX RiLine60 |
| Dimensions | Width: 72.3 mm Height: 119.4 mm Depth: 117.4 mm |
| Clamping area for laminated copper bars (W x H) | 50 x 10 mm |
| To fit busbars | 15 x 10 20 x 10 30 x 10 |
| Rated voltage | 1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL) |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Standards | IEC/EN 61439-1 UL 508 |
| Rated impulse withstand voltage Uimp | 12 kV |
| Rated insulation voltage Ui | 1,000 V |
| IP protection category to IEC 60 529 | IP 2XB |
| Operation humidity max. | 90 % |
| Operating temperature range | -5 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Ambient humidity (non-condensing) | 10...90 % |
| Packs of | 1 pc(s). |
| Net weight | 0.65 |
| Gross weight | 0.688 |

Features

Customs tariff number 85369010

ETIM 9 EC001531

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity