

Rittal – The System.

Faster – better – everywhere.



RX 9362.035

RiLineX NH fuse-switch disconnecter

State: 11/07/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.035 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 95 mm². Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.



Features

| | |
|-----------------|---|
| Model No. | RX 9362.035 |
| Design | For 60 mm busbar systems with electronic fuse monitoring |
| Benefits | Cover: can be locked and prepared for a lead seal Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Colour | RAL 9005 RAL 35745 |
| Supply includes | Connectors for electronic fuse monitoring |

Features

| | |
|---|--|
| For bar systems with centre-to-centre spacing | 60 mm |
| Cable outlet | Top/bottom |
| Type of electrical connection | Box terminal |
| Fuse inserts | NH 00 NH 000 |
| Rated insulation voltage U_i | 1,000 V |
| Rated operating voltage | 690 V AC |
| For NH size | 00 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts) |
| Dimensions | Width: 106 mm Height: 229.5 mm Depth: 104.5 mm |
| Operating temperature range | -5 °C...35 °C |
| Storage temperature range | -25 °C...70 °C |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| To fit busbar system | RiLineX RiLine60 |
| Number of poles | 3-pole |
| Utilisation category | AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A) |
| Contamination level | 3 |
| with electronic fuse monitoring | Yes |
| IP protection category to IEC 60529 | IP 2XB |
| Fire load | 16.6 MJ/m ² |

Features

| | |
|--|---|
| Connection of round conductors, fine wire without wire end ferrule | 1.5 - 95 mm ² |
| Connection of round conductors, fine wire with wire end ferrule | 1.5 - 95 mm ² |
| Heat loss max. | 22 W |
| Heat loss per fuse insert (max.) | 12 W |
| Packs of | 1 pc(s). |
| Net weight | 1.155 kg |
| Gross weight | 1.175 kg |
| Copper weight (kg per piece) | 0.409 |
| PCF per pack (cradle-to-gate) | 7.86 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001040 |
| Product description | RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 95 mm ² . Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring. |

Approvals

| | |
|--------------|--|
| Approvals | CQC-CCC |
| Explanations | Declaration of conformity PCF-declaration |