

# Rittal – The System.

Faster – better – everywhere.



## SV 9345.400 Fuse holders

State: 25/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.400 - Fuse holders 61 A to 400 A

3-pole, for busbar systems with 60 mm bar centre distance.

## Features

Model No.	SV 9345.400
Design	For category J fuse type
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Connection for round conductor	AWG 4/0 – MCM 600
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
For fuse type (class)	J
Rated operating current max.	400 A
Rated operating current (min.)	201 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-8
Note	UL (listed accessory) is met when using the fuse holder on RiLine busbar systems
Standards	UL 508
Dimensions	Width: 250 mm Height: 328 mm
To fit fuses	Diameter: 54 mm Length: 181 mm
To fit busbars	Height: 5, 10 mm

# Features

---

Electrical ratings UL (SCCR)	100 kA - 600 V, Fuse Class J max. 400 A, JDDZ/7
Number of poles	3-pole
Packs of	1 pc(s).
Net weight	5 kg
Gross weight	5.32 kg
Copper weight (kg per piece)	2.106
Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27400613
Product description	SV Fuse holder, Class J, 201-400 A, 600 V, 3-pole, (60 mm)

---

# Approvals

---

Approvals	C-UR UL + C-UL (listed) UR + C-UR (recognized)
-----------	--

# Tender text

Fuseholder Class J, 201 - 400A  
Fuse holder Class J, 201 - 300A, 3-pole, for  
busbar thickness 5 / 10 mm and PLS 800 / 1600  
Type of connection  
Box terminal , round conductor AWG 3/0 - MCM 600  
System  
RiLine Class