

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.233 Digital input module

State: 15/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.233 - Digital input module REM 800-DI 14

The digital input module extends the functional scope of the REM 801 network analyser by a further 14 digital inputs.

## Features

Model No.	SV 9393.233
Operating temperature range	-10 °C...55 °C
Storage temperature range	-25 °C...70 °C
Ambient humidity (non-condensing)	5...25 %
Contamination level	2
Counter frequency max.	20 Hz
Input signal low	0...5 V DC
Input signal high	18...28 V DC
IP protection category to IEC 60529	IP 20
For mounting on support rails	Yes
Connection of round conductors, fine wire without wire end ferrule	0.2 - 1.5 mm <sup>2</sup>
Connection of round conductors, single-wire	0.2 - 1.5 mm <sup>2</sup>
Connection of round conductors, multi-wire	0.2 - 1.5 mm <sup>2</sup>
Connection for round conductor	AWG 16 - 24
Packs of	1 pc(s).
Net weight	0.29 kg
Gross weight	0.295 kg
Customs tariff number	85389099

# Features

---

Product description

SV Digital input module REM 800-DI 14

# Approvals

---

Explanations

Declaration of conformity