

Rittal – The System.

Faster – better – everywhere.



RX 9360.600

RiLineX CB component adaptor

State: 9/09/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.600 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.

Features

| | |
|--------------------------------------|---|
| Model No. | RX 9360.600 |
| Design | universal |
| Benefits | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 9005 RAL 35745 |
| Supply includes | 3 connection space covers |
| IP protection category to IEC 60 529 | IP 2XB |
| Rated impulse withstand voltage Uimp | 12 kV |
| Rated voltage | 690 V AC 690 V DC 600 V AC (UL) |
| Rated insulation voltage | 1,000 V |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Number of poles | 3-pole |

Features

| | |
|-----------------------------------|--|
| Cable outlet | Bottom |
| Type of electrical connection | Box terminal |
| To fit manufacturer (model) | ABB (A1, S2, T1, T2, XT1, XT2, FD63/FD160) BTicino (M1 160) Chint (NM8N-125, NM1-63H, NM1-125H, NXM-63S, NXM-125S, NXM-160S, NXMS-160) Eaton (NZM1) Fuji Electric (BW125JAG-3P) Hager (P160) Himel (HDM3-100F/N, HDM3L-125) Hyundai Electric (100AF, 125AF, 125D, 160D AF) Legrand (DPX 160, DPX 250 ER, DPX ³ 160) LS Electric (100AF, 125AF, TE100, TD100, TE160, TD160) Mitsubishi (NF63-SV, NF125-SV) OEZ (BC160) Rockwell (140G-C2C3-D10, 140G-C2C3-D12, 140-C2E3-D16, 140G-H0F3-D10, 140G-H0F3-D12, 140G-H0F3-D16) Sassini (3SM8L-100) Schneider (NSC100N, NSXm50, NSXm100, NSXm160, NSXm250, NSE100) Schrack (MC1) Siemens (3VA10, 3VA11) Terasaki (E125, S125) |
| To fit busbar system | RiLineX RiLine60 |
| Fundamental frequency | 50...60 Hz |
| Ambient humidity (non-condensing) | 10...90 % |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Operating temperature range | -25 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Dimensions | Width: 81 mm Height: 252 mm Depth: 63 mm |

Features

| | |
|------------------------------|---------------|
| Packs of | 1 pc(s). |
| Net weight | 0.92 |
| Gross weight | 1.22 |
| Copper weight (kg per piece) | 0.375 |
| Customs tariff number | 85369095 |
| EAN | 4028177997103 |
| ETIM 9 | EC001531 |

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|